

3-fold common mode NANOPERM® chokes



Types	Inom free convection	Inom' forced cooling	Isat* /mA	L _N @ 10 kHz [mH]	L _S [μH]	R _{cu} [mΩ]	Pin Ø [mm]	H x B x T [mm]	Design
MB-074¹	3,5	5	80	3 x 6	~ 20	< 40	0,8	38 x 36 x 21	upright
MB-049¹	5	7	60	3 x 8	~ 60	< 36	1,12	42 x 42 x 27	flat
MB-650¹	10	14	110	3 x 11	~ 56	< 15	1,6	60 x 60 x 29	flat
MB-687	12	17	450	3 x 2,5	~ 7	< 9	1,25	47,5 x 47 x 26	upright
MB-051**	12	17	150	3 x 5	~25	<8,6	1,8	59x59x27	flat
MB-652	17	24	300	3 x 3	~ 30	< 7,9	1,8	69 x 69 x 29,5	flat
MB-637	14	20	80	3 x 4,4	~ 12	< 5,5	1,4	48,5 x 48,5 x 26	flat
MB-540¹	15	20	85	3 x 15	~ 16	< 7,0	1,8	59,5 x 59,5 x36,5	flat
MB-617	16	22	90	3 x 11	~ 9	< 6	1,8	52x52x34	flat
MB-634	20	28	400	3 x 1,7	~ 14	< 4,85	2,0	60 x 30 x 60	upright
MB-427	20	28	4760	3x0,31	~8	<2,6	2,5	99,5x99,5x38	flat
MB-653	22	31	270	3 x 4	~ 19	< 4,8	2,24	69 x 69 x 37	flat
MB-157	25	35	300	3 x 6,2	~ 22	< 5,5	2,36	75 x 75 x 34	flat
MB-043	22	31	300	3 x 1,5	~8	< 2,6	2,5	60 x 60 x 30	flat
MB-054	27	38	300	3 x 3,2	~ 9	< 2,6	3,0	73 x 73 x 35	flat
MB-367	28	40	800	3 x 1,2	~ 0,7	< 1,8	3,0	70 x 45 x 70	upright
MB-047	30	42	350	3 x 4	~ 20	< 3,8	5,0	81 x 81 x 62	flat
MB-691	35	50	150	3 x 3	~ 4	< 1,6	2,5	60 x 60 x 34	flat
MB-426	45	64	6660	3 x 0,16	~4,5	<0,95	2x2,5	99,5x99,5x38	flat
MB-656¹	60	85	450	3 x 3,5	~ 17	< 1,35	2x3,35	115 x 115 x 50	flat
MB-657¹	100	140	500	3 x 2,5	~ 10	< 0,85	11,5	130 x 130 x 55	flat
MB-058¹	160	225	1200	3 x 2	~ 10	< 0,5	22,5	158 x 158 x 75	flat

For all information no liability assumed.

*Saturation Current Isat of NANOPERM®: Peak value of the exiting current when the initial inductance level is dropped to 10 per cent, see www.magnetec.de. ¹preliminary. **:Discontinued model

Overtemperature needs to be checked in the application. Environment temperature usually at 70°C, see datasheets, at another environment temperature, the new nom. current can be estimated acc. to the derating theory: <http://www.magnetec.de/fileadmin/pdf/derating.pdf>. In forced cooling condition, double Rth value is assumed.

MAGNETEC GmbH


Industriestrasse 7, D-63505 Langenselbold, Germany

Fon: +49 6184 9202-0 / Fax: +49 6184 9202-20


E-Mail: magnetec@magnetec.de

3-fold common mode NANOPERM® chokes

Example choke – weight and size comparison Ferrite vs. NANOPERM® choke:



Diff. example choke - performance comparison of a NANOPERM® choke vs. Ferrite based choke:



With the same core size NANOPERM® offers significantly improved attenuation levels up to the MHz range. For typical impedances vs. frequency charts, please visit www.magntec.de.

Our Chokes are based on tape wound cores based on the nanocrystalline softmagnetic material **NANOPERM®**. Compared to chokes made of ferrite cores, the following benefits are achieved:

- **High impedance and advanced EMI suppression**
- **Higher saturation flux density**
- **Less temperature sensitive**
- **higher max. component temp (130°C)**

Chokes are available for the nominal current range from 3,5 – 160 Amps, designed acc. to EN60938-1.

The plastic materials fulfill UL-94 V0 and are UL listed.

MAGNETEC GmbH

Industriestrasse 7, D-63505 Langenselbold, Germany
 Fon: +49 6184 9202-0 / Fax: +49 6184 9202-20
 E-Mail: magnetec@magnetec.de